



More information on the website
mirror.radwag.com/en/info,w1,089
















MYA 21.5Y.P Microbalance

WL-109-0023



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Percent Weighing
-  Peak hold
-  Statistics
-  IR sensors
-  GLP Procedures
-  Pipettes Calibration
-  Air density correction
-  Moveable range
-  Differential weighing
-  Ambient conditions monitoring
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters	
Maximum capacity [Max]	21 g
Minimum load	0.1 mg
Readability [d]	1 µg
Verification unit [e]	1 mg
Tare range	-21 g
Minimum weight (USP)	2 mg

Metrological parameters	
Minimum weight (U=1%, k=2)	0.2 mg
Standard repeatability [Max]	3 µg
Standard repeatability [5% Max]	1 µg
Permissible repeatability [Max]	4 µg
Permissible repeatability [5% Max]	1.6 µg
Linearity	±7 µg
Eccentric load deviation	7 µg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times R_t$
Stabilization time	~ 5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, terminal, weighing pan, weighing pan shield, glass vessel, evaporation ring, glass lid, additional glass lid, glass lid, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø 90×90 mm
Capacity	11 ml
Weighing pan dimensions	ø26 mm
Packaging dimensions W x D x H	750×492×595 mm
Net weight	10.6 kg
Gross weight	16.5 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A Max; 15V DC 2.4A Balance: 12 – 15V DC 1.4A max; 9 – 17W*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3 °C / 1 h (±1 °C / 8 h)
Relative humidity	40% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* Power consumption depends on the terminal configuration as well as the number and type of external devices connected.

The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Accessories (Additional Fee)

MediaBox
 RFID Tags
 Antivibration Tables
 Power Adapters
 Additional modules
 Anti-Draft Chamber for Microbalances
 Automatic Variable-Volume Pipettes
 Professional Weighing Tables
 Antistatic ionizer
 Protective cover for balances

Barcode scanners
 Workstation for Pipettes Calibration
 RS 232, RS 485 cables
 Label Printers
 Chamber for filter weighing
 THBR 2.0 System - Ambient Conditions Monitoring
 Receipt Printer
 Fingerprint Reader
 RS 232 – USB Converter

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- R-Pipettes [WX-010-0026]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

Device dimensions W x D x H

