



MYA 21.5Y.P Microbalance
















WL-109-0023

More information on the website
mirror.radwag.com/us/info,w1,089



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Percent Weighing
-  Peak hold
-  Statistics
-  IR sensors
-  GLP Procedures
-  Pipettes Calibration
-  Air density correction
-  Moveable range
-  Differential weighing
-  Ambient conditions monitoring
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters	
Maximum capacity [Max]	21 g
Minimum load	0,1 mg
Readability [d]	1 µg
Verification unit [e]	1 mg
Tare range	-21 g
Minimum weight (USP)	2 mg

Metrological parameters	
Minimum weight (U=1%, k=2)	0,2 mg
Standard repeatability [Max]	3 µg
Standard repeatability [5% Max]	1 µg
Permissible repeatability [Max]	4 µg
Permissible repeatability [5% Max]	1,6 µg
Linearity	±7 µg
Eccentric load deviation	7 µg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	~ 5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, terminal, weighing pan, weighing pan shield, glass vessel, evaporation ring, glass lid, additional glass lid, glass lid, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø 90×90 mm
Capacity	11 ml
Weighing pan dimensions	ø26 mm
Packaging dimensions W x D x H	750×492×595 mm
Net weight	10,6 kg
Gross weight	16,5 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A Max; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max; 9 – 17W*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3 °C / 1 h (±1 °C / 8 h)
Relative humidity	40% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Accessories (Additional Fee)

MediaBox
RFID Tags
Antivibration tables
Power Adapters
Additional modules
Anti-Draft Chamber for Microbalances
Automatic Variable-Volume Pipettes
Professional Weighing Tables
Antistatic ionizer
Protective cover for balances

Barcode scanners
Workstation for pipettes calibration
Balance Storage Case
RS 232, RS 485 cables
Label Printers
Chamber for filter weighing
THBR 2.0 System - Ambient Conditions Monitoring
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- R-Pipettes [WX-010-0026]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions W x D x H

