



More information on the website  
[mirror.radwag.com/en/info,w1,091](https://mirror.radwag.com/en/info,w1,091)

# PLC/6/F1 Platform



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	6 kg
Readability [d]	2 g
Construction	
Protection class	IP 65
Construction	mild steel St3S
Weighing pan material	Stainless steel AISI304
Physical parameters	
Weighing pan dimensions	300×300 mm
Packaging dimensions	570×390×170 mm

**Readability accuracy** – expected value, dependent on the parameters of the measuring transmitter used.




# Accessories



CY10 Scales for PGC  
 PUE CY10 Weighing Terminal  
 CY10 Multifunctional Scale  
 PUE 5 Weighing Terminal  
 CY10 Precision Balance  
 PUE C32 Weighing Terminal

PUE 7.1 Weighing Terminal  
 PUE HX7 Weighing Terminal  
 PUE C315 Weighing Terminal  
 PUE HY10 Weighing Terminal  
 PUE H315 Weighing Terminal


## Device dimensions





PL/D2



PLC/F1



PLC/C2  
PLC/C3



PL/H  
PL/HR

Platform type	A1	A2	H
PL/D2	238	216	82±3
PLC/F1	300	300	70±3
PLC/C2	402	502	103±3
PLC/C3	701	501	130±5
PL/H1 / PL/HR1	150	200	85±3
PL/H2 / PL/HR2	250	300	103±3
PL/H3 / PL/HR/3	410	410	98±3
PL/H3/5 / PL/HR/3/5	400	600	155±3
PL/H4 / PL/HR/4	500	500	155±3
PL/H5 / PL/HR/5	600	600	155±3
PL/H6	800	800	135±3

dimensions in mm