



More information on the website
mirror.radwag.com/ja/info,w1,091

PLC/6/F1

WX-009-0096



The drawings, photos and graphics used are for illustrative purposes only.


[Max]	6 kg
[d]	2 g
	IP 65
	St3S
	AISI304
	300×300 mm
	570×390×170 mm





(Additional Fee)

PGC CY10
 PUE CY10
 CY10
 PUE 5
 CY10
 PUE C32



PUE 7.1
 PUE HX7
 PUE C315
 PUE HY10
 PUE H315




PL/D2



PLC/F1



PLC/C2
PLC/C3



PL/H
PL/HR



Platform type	A1	A2	H
PL/D2	238	216	82±3
PLC/F1	300	300	70±3
PLC/C2	402	502	103±3
PLC/C3	701	501	130±5
PL/H1 / PL/HR1	150	200	85±3
PL/H2 / PL/HR2	250	300	103±3
PL/H3 / PL/HR3	410	410	98±3
PL/H3/5 / PL/HR/3/5	400	600	155±3
PL/H4 / PL/HR4	500	500	155±3
PL/H5 / PL/HR5	600	600	155±3
PL/H6	800	800	135±3

dimensions in mm