



More information on the website
mirror.radwag.com/tr/info,w1,0E1

TDM Metal Detectors

WX-018-0007



The drawings, photos and graphics used are for illustrative purposes only.

Fonksiyonlar



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit
measurement



GLP Procedures



Animal weighing



ALIBI Memory

Genel Açıklama

Conveyors that are equipped with metal detectors create flexible systems for control and separation of contaminated products. They make production process compatible with the requirements of HACCP in case of final production stage, and control over equipment in case of inter-operational control. Control system are prepared and configured according to customer requirements.

Application:

The device designed to control products for their metal contamination. Depending on configuration the control set can automatically separate contaminated goods, stop technological line or signal an alarm for a supervising unit. Metal detectors are applicable in practically every branch of industry. They can operate in

random industrial conditions, and control random kinds of goods, independently on their type or temperature.

Functions:

Main functions of TDM metal detector:

Control of goods for their metal contamination; Optical and acoustic signaling of metal contamination in goods; Stoppage of technological line in case of a defect; Discrimination set; Castors for easy device transport.

İle uyumlu (Additional Fee)

Antivibrasyon masaları
RS 232, RS 485 Kabloları

AP2-1 Güç döngüsü çıkışı
RS 232 – RS 485 Dönüştürücü