



More information on the website
mirror.radwag.com/en/info,w1,0RI

C315.6/15.D-1 Baby Scale

WM-001-1010



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Internal battery



Peak hold



GLP Procedures



ALIBI Memory

Datasheet

| Metrological parameters | |
|--------------------------------|--------------------|
| Maximum capacity [Max] | 6 / 15 kg |
| Readability [d] | 2 / 5 g |
| Tare range | -15 kg |
| OIML Class | III |
| Physical parameters | |
| Display | 4.3" LCD (backlit) |
| Packaging dimensions W x D x H | 600x520x180 mm |
| Net weight | 3.69 kg |
| Gross weight | 5.5 kg |

| Communication interface | |
|-----------------------------|-------------------------------------|
| Communication interface | RS232 |
| Electrical parameters | |
| Power supply | 100 – 240 V AC 50/60 Hz and battery |
| Power consumption max. | 5 W |
| Operation time on batteries | up to 8 h |
| Environmental conditions | |
| Operating temperature | 0 – +40 °C |
| Relative humidity | 10% – 85% RH no condensation |

According to MDR regulations, this scale is not a medical device.



Additional fee for verification

Accessories (Additional Fee)

Power Adapters

RS 232 cables (scale - printer)

Cigarette lighter receptacle power supply cables

Displays

RS 232, RS 485 cables

RS 232 – Ethernet Converter

RS 232 – USB Converter

RS 232 – RS 485 Converter

Receipt Printer

Software (Additional Fee)

• RAD Key [WX-010-0005]

• Scale Editor 2.1 [WX-010-0173]

• R-Lab [WX-010-0080]

Device dimensions W x D x H

