



More information on the website  
[mirror.radwag.com/es/info,w1,0XU](http://mirror.radwag.com/es/info,w1,0XU)

## CK-02/3 Transponder Card Reader

WX-004-0147



The drawings, photos and graphics used are for illustrative purposes only.

### Descripción

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/3 is designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal. Area of Use: Additional equipment of load cell based industrial scales; Identification of weighing instrument operator; Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing. Intended Use: Designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal.

### Trabaja con (Additional Fee)

Balanza de alta resolución inoxidable HY10.HRP.H  
Báscula multifuncionale inoxidable TMX H  
Báscula multifuncional TMX  
Báscula multifuncional HY10  
Báscula multifuncionale inoxidable HY10 H  
Balanza de alta resolución PUE 7.1.HRP  
Balanza de alta resolución HY10.HRP

Balanza HY10.H para CCE  
Balanzas de control rotativas  
Balanzas dinámicas DWT/RC/HYF  
Balanzas de control para grandes cargas  
Terminal de pesaje PUE 5  
Báscula de plataforma impermeable H315 H  
Basculas de carriles