



More information on the website
mirror.radwag.com/it/info,w1,0XU

CK-02/3 Transponder Card Reader

WX-004-0147



The drawings, photos and graphics used are for illustrative purposes only.

Caratteristiche generali

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/3 is designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal. Area of Use: Additional equipment of load cell based industrial scales; Identification of weighing instrument operator; Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing. Intended Use: Designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal.

Compatibile con (Additional Fee)

Bilance ad alta risoluzione in acciaio inox HY10.HRP H
Bilancia multifunzione in acciaio inox TMX H
Bilancia multifunzione TMX
Bilancia multifunzione HY10
Bilancia multifunzione in acciaio inox HY10 H
Bilance ad alta risoluzione PUE 7.1 HRP
Bilance ad alta risoluzione HY10.HRP

Bilance HY10.H per controllo CPC
Selezionatrici ponderali rotanti
Sistemi automatici controllo peso DWT/RC/HYF
Selezionatrici ponderali per carichi di grandi dimensioni
Terminale di pesata PUE 5
Bilancia a piattaforma impermeabile H315 H
Bilance di pesatura su rotaia