



More information on the website  
[mirror.radwag.com/it/info,w1,0XU](http://mirror.radwag.com/it/info,w1,0XU)

## CK-02/3 Transponder Card Reader

WX-004-0147



The drawings, photos and graphics used are for illustrative purposes only.

### Caratteristiche generali

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/3 is designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal. Area of Use: Additional equipment of load cell based industrial scales; Identification of weighing instrument operator; Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing. Intended Use: Designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal.

### Compatibile con (Additional Fee)

Bilance ad alta risoluzione in acciaio inox HY10.HRP H  
Bilancia multifunzione in acciaio inox TMX H  
Bilancia multifunzione TMX  
Sistemi automatici controllo peso DWT/RC/HYF  
Bilancia multifunzione HY10  
Bilancia multifunzione in acciaio inox HY10 H  
Bilance ad alta risoluzione PUE 7.1 HRP

Bilance ad alta risoluzione HY10.HRP  
Bilance HY10.H per controllo CPC  
Selezionatrici ponderali rotanti  
Terminale di pesata PUE 5  
Bilancia a piattaforma impermeabile H315 H  
Selezionatrici ponderali per carichi di grandi dimensioni  
Bilance di pesatura su rotaia