



More information on the website  
[mirror.radwag.com/tr/info,w1,0XU](http://mirror.radwag.com/tr/info,w1,0XU)

## CK-02/3 Transponder Card Reader

WX-004-0147



The drawings, photos and graphics used are for illustrative purposes only.

### Genel Açıklama

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/3 is designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal. Area of Use: Additional equipment of load cell based industrial scales; Identification of weighing instrument operator; Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing. Intended Use: Designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal.

### İle uyumlu (Additional Fee)

HY10.HRP.H Paslanmaz çelik Yüksek Çözünürlüklü Teraziler  
TMX H TMX Çok Fonksiyonlu Paslanmaz çelik terazi  
TMX Çok Fonksiyonlu Terazi  
HY10 Çok Fonksiyonlu Terazi  
HY10 H Çok Fonksiyonlu Paslanmaz çelik terazi  
PUE 7.1.HRP Yüksek Çözünürlüklü Teraziler  
HY10.HRP Yüksek Çözünürlüklü Teraziler

PUK için HY10.H terazileri  
Rotasyonel kontrol terazileri  
DWT/RC/HYF Kontrol terazileri  
Büyük yükler için kontrol terazileri  
PUE 5 tartım terminali  
H315 H Su geçirmez platform kantarları  
Asma ray kantarları