



More information on the website  
[mirror.radwag.com/us/info,w1,0XU](https://mirror.radwag.com/us/info,w1,0XU)

# CK-02/3 Transponder Card Reader

WX-004-0147



The drawings, photos and graphics used are for illustrative purposes only.

## Overview

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/3 is designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal. **Area of Use:** • Additional equipment of load cell based industrial scales; • Identification of weighing instrument operator; • Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing.

### Intended Use:

Designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal.

## Compatible with (Additional Fee)

HY10.HRP.H High Resolution Scale  
 TMX H Stainless steel Multifunctional Scale  
 TMX Multifunctional Scale  
 DWT/RC/HYF Checkweighers  
 HY10 Multifunctional Scale  
 HY10 H Stainless Steel Multifunctional Scale  
 PUE 7.1.HRP High Resolution Scale

HY10.HRP High Resolution Scale  
 HY10.H scales for PGC  
 Rotational Control Scales  
 PUE 5 Weighing Terminal  
 H315 H Waterproof Platform Scale  
 Control Scales for Large Loads