



More information on the website
mirror.radwag.com/us/info,w1,0XU

CK-02/3 Transponder Card Reader

WX-004-0147



The drawings, photos and graphics used are for illustrative purposes only.

Overview

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/3 is designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal. Area of Use: • Additional equipment of load cell based industrial scales; • Identification of weighing instrument operator; • Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing.

Intended Use:

Designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal.

Compatible with (Additional Fee)

HY10.HRP.H High Resolution Scale
TMX H Stainless steel Multifunctional Scale
TMX Multifunctional Scale
HY10 Multifunctional Scale
HY10 H Stainless Steel Multifunctional Scale
PUE 7.1.HRP High Resolution Scale
HY10.HRP High Resolution Scale

HY10.H scales for PGC
Rotational Control Scales
DWT/RC/HYF Checkweighers
Control Scales for Large Loads
PUE 5 Weighing Terminal
H315 H Waterproof Platform Scale
Track Scales

