



More information on the website
mirror.radwag.com/us/info,w1,13S

DWT/RC 60/HYF Checkweigher

WK-106-0033



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]	60 kg
Minimum load	400 g
Readability [d]	20 g
Tare range	-60 kg
Physical parameters	
Display	10" graphic colour touchscreen
Weighing platform height	800 ± 50 mm (other levels of platform on client requirement)
Construction	
Protection class	IP 66 / 67
Operating temperature	-10 – +40 °C
Features of use	
Conveyor velocity	0,1 – 0,5 m/s



Accessories (Additional Fee)

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Barcode scanners

Label Printers

!Keypad, external switches

Receipt Printer

USB cable (scale - printer)

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]