



More information on the website  
[mirror.radwag.com/us/info,w1,13U](https://mirror.radwag.com/us/info,w1,13U)

# HX7.4N.300.H4.LD Multifunctional Stainless Steel Ramp Scale

WP-227-0024



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Dosing



Percent Weighing



Parts counting



Formulation



Replaceable unit



ALIBI Memory

## Datasheet

| Maximum capacity [Max]                 | 300 kg            |
|----------------------------------------|-------------------|
| Minimum load                           | 2 kg              |
| Readability [d]                        | 100 g             |
| Verification unit [e]                  | 100 g             |
| Tare range                             | -300 kg           |
| Max readability for non-verified scale | 50 g              |
| OIML Class                             | III               |
| Physical parameters                    |                   |
| Display                                | 7" graphic colour |

| Physical parameters            |                                                                                                                                                     |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| Cable length                   | 3 m                                                                                                                                                 |
| Weighing pan dimensions        | 1500×1500 mm                                                                                                                                        |
| Packaging dimensions W x D x H | 2040×1900×580 mm                                                                                                                                    |
| Net weight                     | 280 kg                                                                                                                                              |
| Gross weight                   | 450 kg                                                                                                                                              |
| Construction                   |                                                                                                                                                     |
| Protection class               | IP 66 / 69 construction, IP 66 / 67 terminal                                                                                                        |
| Keypad                         | membrane                                                                                                                                            |
| Construction                   | Stainless steel AISI304                                                                                                                             |
| Communication interface        | RS232, USB-A, 4IN, 4OUT, Ethernet, Modbus RTU                                                                                                       |
| Optional interfaces            | USB (M12 4P), Ethernet, module RS485, module RS232, module Profibus (Dp SLAVE), PROFINET (RRJ45), EtherNet/IP (RRJ45), 12 IN, 12 OUT, 4-20mA, 0-10V |
| Power supply                   | 100 – 240 V AC 50/60 Hz                                                                                                                             |
| Power consumption max.         | 25 W                                                                                                                                                |
| Optional power supply          | 12 – 24 V DC                                                                                                                                        |
| Operating temperature          | -10 – +40 °C                                                                                                                                        |
| Storage temperature            | -10 – +50 °C                                                                                                                                        |
| Relative humidity              | 10% – 80% RH no condensation                                                                                                                        |
| Indicator                      | PUE HX7                                                                                                                                             |
| Number of buttons              | 22                                                                                                                                                  |
| Features of use                |                                                                                                                                                     |
| Max number of platforms        | 2                                                                                                                                                   |



Additional fee for verification



## Accessories (Additional Fee)

RS 232 cables (scale - printer)  
 RS 232 cables (scale - ZEBRA printer)  
 Displays  
 Power Adapters  
 RS 232, RS 485 cables  
 USB cable (scale - printer)  
 IN/OUT Cables  
 Barcode scanners


Label Printers  
 Stands, wall mounting kits and mounting brackets  
 Keypad, external switches  
 USB adapter  
 Receipt Printer  
 Additional Weighing platforms Module  
 RS 232 – USB Converter  
 Additional modules

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- Alibi Reader PC Software [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]

## Device dimensions W x D x H



|                   | A [mm] | B [mm] | C [mm] | D [mm] |
|-------------------|--------|--------|--------|--------|
| HX7.4N.150.H1.LD  | 840    | 860    | 45     | 426    |
| HX7.4N.300.H1.LD  | 840    | 860    | 45     | 426    |
| HX7.4N.600.H1.LD  | 840    | 860    | 45     | 426    |
| HX7.4N.150.H2.LD  | 1100   | 1200   | 45     | 426    |
| HX7.4N.300.H2.LD  | 1100   | 1200   | 45     | 426    |
| HX7.4N.600.H2.LD  | 1100   | 1200   | 45     | 426    |
| HX7.4N.300.H3.LD  | 1200   | 1500   | 45     | 426    |
| HX7.4N.600.H3.LD  | 1200   | 1500   | 45     | 426    |
| HX7.4N.1500.H2.LD | 1100   | 1200   | 52     | 476    |
| HX7.4N.1500.H3.LD | 1200   | 1500   | 52     | 476    |
| HX7.4N.300.H4.LD  | 1500   | 1500   | 52     | 476    |
| HX7.4N.600.H4.LD  | 1500   | 1500   | 52     | 476    |
| HX7.4N.1500.H4.LD | 1500   | 1500   | 52     | 476    |