



More information on the website
mirror.radwag.com/en/info,w1,140

PUE CY10 Weighing Terminal

WX-008-0217



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Autotest



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



Newton unit measurement



Statistics



Checkweighing



IR sensors



GLP Procedures



Animal weighing



Pipettes Calibration



Air density correction



Density determination



Differential weighing



Ambient conditions monitoring



Statistical Quality Control



Packaged Goods Control



ALIBI Memory



Wi-Fi

Datasheet

Physical parameters

Display

10" graphic colour touchscreen

Construction	
Protection class	IP 43
Housing	ABS + aluminum
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	12 – 15 V DC
Power consumption	1 A
Metrological parameters	
Maximum quantity of verification units	10000
Minimum voltage per verification unit	0.4 μ V
Maximum voltage per verification unit	3.25 μ V
Minimum load cell impedance	50 Ω
Maximum load cell impedance	1200 Ω
Load cell excitation voltage	5V
Maximum increase of signal	19.5 mV
Connection of load cells	4 or 6 wires + ekran
Environmental conditions	
Operating temperature	-10 – +40 °C
Components and software	
Operating system	Linux
Processor	quad-core Broadcom 1.5 GHz
Memory	16 GB, 2GB RAM
Multiple range	YES
Features of use	
Max number of platforms	max.2

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Compatible with (Additional Fee)

MediaBox
Mild steel powder coated weighing platforms
RFID Tags
Power Adapters
Additional Weighing platforms Module
Additional modules
Platforms in plastic casing

Protective cover for balances
Barcode scanners
RS 232, RS 485 cables
Label Printers
Fingerprint Reader
RS 232 – USB Converter
Receipt Printer

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

Device dimensions W x D x H

