



More information on the website  
[mirror.radwag.com/en/info,w1,1NW](http://mirror.radwag.com/en/info,w1,1NW)

# CY10.60/120.C2.K.M2.PGC Scale

WK-312-1007



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Packaged Goods Control



Wi-Fi

## Datasheet

Metrological parameters	
Maximum capacity [Max]	60 / 120 kg
Minimum load	500 / 1000 g
Readability [d]	10 / 20 g
Verification unit [e]	10 / 20 g
Tare range	-120 kg
Stabilization time	3 s
Adjustment	external

Metrological parameters	
OIML Class	II
Physical parameters	
Leveling system	manual
Display	10" graphic colour touchscreen
Cable length	2.5 m
Weighing pan dimensions	400×500 mm
Packaging dimensions W x D x H	720×620×210 mm
Net weight	13.5 kg
Gross weight	16 kg
Construction	
Protection class	IP 43
Housing	steel + ABS
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.6A max; 10–19W*
Environmental conditions	
Operating temperature	+15 – +30 °C
Storage temperature	-25 – +70 °C
Relative humidity	10% – 80% RH no condensation

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

MediaBox  
Mild steel powder coated weighing platforms  
HRP Platforms High Capacity  
RFID Tags  
Power Adapters  
Additional Weighing platforms Module

Platforms in plastic casing  
Protective cover for balances  
Label Printers  
Receipt Printer  
Fingerprint Reader  
RS 232 – USB Converter

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

## Device dimensions W x D x H

