




More information on the website  
[mirror.radwag.com/us/info,w1,1Q6](https://mirror.radwag.com/us/info,w1,1Q6)

# C32.150.C3.M Multifunctional Scale

WP-120-0032



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Labelling



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Newton unit  
measurement



Statistics



IR sensors



GLP Procedures



Replaceable unit



ALIBI Memory

## Datasheet

| Maximum capacity [Max]                 | 150 kg  |
|----------------------------------------|---------|
| Minimum load                           | 1 kg    |
| Readability [d]                        | 50 g    |
| Verification unit [e]                  | 50 g    |
| Tare range                             | -150 kg |
| Max readability for non-verified scale | 5 g     |
| OIML Class                             | III     |

| Physical parameters            |                                                                |
|--------------------------------|----------------------------------------------------------------|
| Display                        | 5" graphic colour                                              |
| Weighing pan dimensions        | 700×500 mm                                                     |
| Packaging dimensions W x D x H | 730×800×270 mm                                                 |
| Net weight                     | 23,4 kg                                                        |
| Gross weight                   | 27,2 kg                                                        |
| Construction                   |                                                                |
| Protection class               | IP 65 construction, IP 43 terminal                             |
| Construction                   | mild steel St3S                                                |
| Weighing pan material          | Stainless steel AISI304                                        |
|                                |                                                                |
| Communication interface        | 2×RS232, USB-A, USB-B, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi |
|                                |                                                                |
| Power supply                   | 100 – 240 V AC 50/60 Hz                                        |
| Power consumption max.         | 10 W                                                           |
| Optional power supply          | internal rechargeable battery                                  |
| Operation time on batteries    | operation time up to 5 h                                       |
|                                |                                                                |
| Operating temperature          | -10 – +40 °C                                                   |

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



## Accessories (Additional Fee)

Displays

Power Adapters

RS 232 cables (scale - printer)

Cigarette lighter receptacle power supply cables

Barcode scanners

RS 232, RS 485 cables

Label Printers

!Keypad, external switches

Stands, wall mounting kits and mounting brackets

Additional modules

Receipt Printer

AP2-1 Current Loop Unit

## Software (Additional Fee)

• E2R Weighing [WX-010-0099]

• Label Editor R02 [WX-010-0094]



• Scale Editor - EWAG 2.1 [WX-010-0173]

• RAD Key [WX-010-0005]



• Alibi Reader PC Software [WX-010-0114]

• RADWAG Development Studio [WX-010-0104]

Device dimensions W x D x H



C32.C3.K



C32.C3.M