



More information on the website
mirror.radwag.com/us/info,w1,1YD

C32.10.PM Precision Balance

WL-223-0005



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Newton unit measurement



Statistics



IR sensors



Under-pan weighing



GLP Procedures



Animal weighing



Density determination



Replaceable unit



ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	10 kg
Minimum load	0,5 g
Preload range	1 kg
Readability [d]	0,01 g
Verification unit [e]	0,1 g
Tare range	-10 kg

Metrological parameters	
Minimum weight (USP)	8,2 g
Minimum weight (U=1%, k=2)	0,82 g
Repeatability (Max)	0,01 g
Repeatability (5% Max)	0,0041 g
Linearity	±0,025 g
Stabilization time	1 s
Adjustment	internal (automatic)
OIML Class	II
Physical parameters	
Leveling system	manual
Display	5" graphic colour
Weighing pan dimensions	200×185 mm
Packaging dimensions W x D x H	520×520×280 mm
Net weight	10 kg
Gross weight	13,5 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×RS232, USB-A, USB-B, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Balance: 10 – 12V DC 1A max
Environmental conditions	
Operating temperature	+10 – +40 °C

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Accessories (Additional Fee)

Displays

Antivibration tables

Power Adapters

RS 232 cables (scale - printer)

Cigarette lighter receptacle power supply cables

Professional Weighing Tables

Barcode scanners

Under-pan weighing

RS 232, RS 485 cables

Stands, wall mounting kits and mounting brackets

Receipt Printer

AP2-1 Current Loop Unit

Software (Additional Fee)

• E2R Weighing [WX-010-0099]

• Label Editor R02 [WX-010-0094]

• Scale Editor - EWAG 2.1 [WX-010-0173]

• RAD Key [WX-010-0005]

• Alibi Reader PC Software [WX-010-0114]

• RADWAG Development Studio [WX-010-0104]

Device dimensions W x D x H

