



More information on the website
mirror.radwag.com/de/info,w1,25G

Balkenwaage C315.4P2.3000.C

WP-240-0004



The drawings, photos and graphics used are for illustrative purposes only.

Funktionen



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit
measurement



GLP Procedures



Animal weighing



ALIBI Memory

Technische Daten

Messtechnische Parameter	
Wägebereich [Max]	3000 kg
Min. Belastung	20 kg
Ablesbarkeit [d]	1 kg
Eichwert [e]	1 kg
Tarierbereich	-3000 kg
OIML-Klasse	III

Physikalische Parameter		
Display		4,3" LCD (hinterleuchtet)
Kabellänge		3 m + 5 m
Waagschale		2 St. 1,2 m
Abmessungen des Geräts B x T x H		1200×120×85 mm
Gewicht der Waage mit Messgerät		37 kg
Konstruktion		
Schutzart		IP 65 Konstruktion, IP 67 Tensometer, IP 43 Terminal
Kommunikationsschnittstellen		
Schnittstellen		RS232
Optionale Schnittstellen		RS232
Elektrische Parameter		
Stromversorgung		100 – 240 V AC 50/60 Hz + Akkus
Maximaler Leistungsaufnahme		5 W
Akku-Betriebszeit		max 8h
Umgebungsbedingungen		
Umgebungstemperatur		-10 – +40 °C
Relative Luftfeuchtigkeit		10% – 85% RH ohne Kondensation



Additional fee for verification



Zubehör (Additional Fee)

Netzteile
 Kabel RS 232 (Waage – Drucker)
 Wandhalterung, Stativ
 Anschlusskabel für Zigarettenanzünder
 Displays
 Konverter RS 232 – Ethernet


Ausgang der Stromschnittstelle AP2-1
 Kabel RS 232, RS 485
 Konverter RS 232 – USB
 Konverter RS 232 – RS 485
 Thermische Drucker

Software (Additional Fee)

• RAD Key [WX-010-0005]
 • Scale Editor 2.1 [WX-010-0173]

• RLAB [WX-010-0080]

Abmessungen des Geräts B x T x H



Scale type	A	B	H	D
C315.4P2.600.C	120	1200	85	1100
C315.4P2.1500.C	120	1200	85	1100
C315.4P2.3000.C	120	1200	85	1100
C315.4P2.2000.C1	120	2000	105	1900
C315.4P2.2000.C2	120	2500	105	2400
C315.4P2.4000.C1	120	2000	155	1880
C315.4P2.4000.C2	120	2500	155	2380
C315.4P2.6000.C1	120	2000	155	1880
C315.4P2.6000.C2	120	2500	155	2380

dimensions in mm