



More information on the website
mirror.radwag.com/en/info,w1,2DE

C315.100/200.OK-1 Personal Scale

WM-004-1032



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Internal battery



Peak hold



GLP Procedures



ALIBI Memory



BMI

Datasheet

Metrological parameters

| | |
|------------------------|--------------|
| Maximum capacity [Max] | 100 / 200 kg |
| Readability [d] | 50 / 100 g |
| Tare range | -200 kg |
| OIML Class | III |

Physical parameters

| | |
|--------------------------------|--------------------|
| Display | 4.3" LCD (backlit) |
| Cable length | 2.5 m |
| Packaging dimensions W x D x H | 500×420×160 mm |
| Net weight | 6.5 kg |

| Physical parameters | |
|-----------------------------|-------------------------------------|
| Gross weight | 8 kg |
| Communication interface | |
| Communication interface | RS232 |
| Electrical parameters | |
| Power supply | 100 – 240 V AC 50/60 Hz and battery |
| Power consumption max. | 5 W |
| Operation time on batteries | up to 8 h |
| Environmental conditions | |
| Operating temperature | 0 – +40 °C |
| Relative humidity | 10% – 85% RH no condensation |

According to MDR regulations, this scale is not a medical device.



Additional fee for verification

Accessories (Additional Fee)

RS 232 cables (scale - printer)
Cigarette lighter receptacle power supply cables
Displays
RS 232, RS 485 cables

RS 232 – Ethernet Converter
RS 232 – USB Converter
RS 232 – RS 485 Converter
Receipt Printer

Software (Additional Fee)

- RAD Key [WX-010-0005]
- Scale Editor 2.1 [WX-010-0173]

- R-Lab [WX-010-0080]



Device dimensions W x D x H



C315.OW



C315.OR



C315.OK