



More information on the website  
[mirror.radwag.com/en/info,w1,2E2](https://mirror.radwag.com/en/info,w1,2E2)

## CK-02/4 Transponder Card Reader

WX-004-0153



The drawings, photos and graphics used are for illustrative purposes only.

### Overview

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/4 is designed for scales equipped with terminal PUE 7 series. It is installed next to the terminal. Communication through RS232, power supply 5V from scale terminal. Area of Use: Additional equipment of load cell based industrial scales; Identification of weighing instrument operator; Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing. Intended Use: Designed for scales equipped with terminal PUE 7 series. It is installed next to the terminal. Communication through RS232, power supply 5V from scale terminal.

### Compatible with (Additional Fee)

WPY Multifunctional Scale  
WLY Scales for PGC  
WPY Scales for PGC

WLY Precision Balance  
PUE 7.1 Weighing Terminal