



More information on the website  
[mirror.radwag.com/es/info,w1,2E2](https://mirror.radwag.com/es/info,w1,2E2)

# CK-02/4 Transponder Card Reader

WX-004-0153



The drawings, photos and graphics used are for illustrative purposes only.

## Descripción

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/4 is designed for scales equipped with terminal PUE 7 series. It is installed next to the terminal. Communication through RS232, power supply 5V from scale terminal. Area of Use: Additional equipment of load cell based industrial scales; Identification of weighing instrument operator; Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing. Intended Use: Designed for scales equipped with terminal PUE 7 series. It is installed next to the terminal. Communication through RS232, power supply 5V from scale terminal.

## Trabaja con (Additional Fee)

Báscula multifuncional WPY  
 Balanzas WLY para CCE  
 Balanzas WPY para CCE

Balanza de precisión WLY  
 Terminal de pesaje PUE 7.1