



More information on the website
mirror.radwag.com/es/info,w1,2E2

CK-02/4 Transponder Card Reader

WX-004-0153



The drawings, photos and graphics used are for illustrative purposes only.

Descripción

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/4 is designed for scales equipped with terminal PUE 7 series. It is installed next to the terminal. Communication through RS232, power supply 5V from scale terminal. Area of Use: Additional equipment of load cell based industrial scales; Identification of weighing instrument operator; Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing. Intended Use: Designed for scales equipped with terminal PUE 7 series. It is installed next to the terminal. Communication through RS232, power supply 5V from scale terminal.

Trabaja con (Additional Fee)

Báscula multifuncional WPY
Balanzas WLY para CCE
Balanzas WPY para CCE

Balanza de precisión WLY
Terminal de pesaje PUE 7.1