



More information on the website
mirror.radwag.com/it/info,w1,2E2

CK-02/4 Transponder Card Reader

WX-004-0153



The drawings, photos and graphics used are for illustrative purposes only.

Caratteristiche generali

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/4 is designed for scales equipped with terminal PUE 7 series. It is installed next to the terminal. Communication through RS232, power supply 5V from scale terminal. Area of Use: Additional equipment of load cell based industrial scales; Identification of weighing instrument operator; Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing. Intended Use: Designed for scales equipped with terminal PUE 7 series. It is installed next to the terminal. Communication through RS232, power supply 5V from scale terminal.

Compatibile con (Additional Fee)

Bilancia multifunzione WPY
 Balance WLY per controllo CPC
 Balance WPY per controllo CPC

Bilancia di precisione WLY
 Terminale di pesata PUE 7.1