

## **CK-02/4 Transponder Card Reader**





The drawings, photos and graphics used are for illustrative purposes only.

## **Overview**

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/4 is designed for scales equipped with terminal PUE 7 series. It is installed next to the terminal. Communication through RS232, power supply 5V from scale terminal. Area of Use: • Additional equipment of load cell based industrial scales; • Identification of weighing instrument operator; • Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing.

## Intended Use:

Designed for scales equipped with terminal PUE 7 series. It is installed next to the terminal. Communication through RS232, power supply 5V from scale terminal.

## **Compatible with (Additional Fee)**

WPY Multifunctional Scale WLY Scales for PGC WPY Scales for PGC

**WLY Precision Balance** PUE 7.1 Weighing Terminal