



More information on the website  
[mirror.radwag.com/us/info,w1,2E2](https://mirror.radwag.com/us/info,w1,2E2)

# CK-02/4 Transponder Card Reader

WX-004-0153



The drawings, photos and graphics used are for illustrative purposes only.

## Overview

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/4 is designed for scales equipped with terminal PUE 7 series. It is installed next to the terminal. Communication through RS232, power supply 5V from scale terminal. **Area of Use:** • Additional equipment of load cell based industrial scales; • Identification of weighing instrument operator; • Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing.

### Intended Use:

Designed for scales equipped with terminal PUE 7 series. It is installed next to the terminal. Communication through RS232, power supply 5V from scale terminal.

## Compatible with (Additional Fee)

WPY Multifunctional Scale  
 WLY Scales for PGC  
 WPY Scales for PGC

WLY Precision Balance  
 PUE 7.1 Weighing Terminal