



More information on the website  
[mirror.radwag.com/en/info,w1,2TV](http://mirror.radwag.com/en/info,w1,2TV)

# High Resolution Platforms

## PL.150.1.HRP.EX

WX-009-0335



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

### Metrological parameters

Maximum capacity [Max]	150 kg
Preload range	30 kg
Readability [d]	1 g
Tare range	-150 kg
Repeatability	1.5 g
Linearity	±3 g
Adjustment	internal (automatic)

### Physical parameters

Cable length	10 m
Weighing pan dimensions	800×600 mm
Packaging dimensions W x D x H	1000×800×307 mm
Net weight	71.5 kg
Gross weight	119 kg

Construction	
Protection class	IP 67
ATEX Certification	II 3G Ex ic IIB T4 Gc
IECEX Certification	Ex ic IIB T4 Gc
Construction	mild steel St3S
Weighing pan material	Stainless steel AISI304
Communication interface	
Communication interface	RS485
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Environmental conditions	
Operating temperature	+10 – +40 °C
Relative humidity	15% – 80%



## Accessories (Additional Fee)

PUE HX5.EX Weighing Terminal  
 Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX  
 Weighing Terminal

Receipt Printer

## Software (Additional Fee)

- MWMH Manager [WX-010-0103]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]

## Device dimensions W x D x H



PL.16 - 32.HRP



PL.62-2000.HRP

Scale type	A1	A2	H
PL.(16-32).HRP	360	280	180±5
PL.(62-150).HRP	500	400	180±5
PL.150.2.HRP	500	500	180±5
PL.(150.1-300).HRP	800	600	180±5
PL.(300.1-1100).HRP	1000	800	180±5
PL.(2000).HRP	1250	1000	180±5

Dimensions in mm