



More information on the website
mirror.radwag.com/en/info,w1,2VF

C315.4P.1500.C Pallet Scale

WP-239-0001



The drawings, photos and graphics used are for illustrative purposes only.

Functions

 Plus/Minus Control

 Percent Weighing

 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 GLP Procedures

 Animal weighing

 ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 kg
Minimum load	10 kg
Readability [d]	500 g
Tare range	-1500 kg
Max readability for non-verified scale	500 g
OIML Class	III

Physical parameters		
Display		4.3" LCD (backlit)
Cable length		3 m
Weighing pan dimensions		840×1200 mm
Device dimensions W x D x H		1322×840×85 mm
Packaging dimensions W x D x H		1400×900×430 mm
Scale mass with indicator		43 kg
Construction		
Protection class		IP 65 construction, IP 67 cell, IP 43 terminal
Communication interface		
Communication interface		RS232
Optional interfaces		RS232
Electrical parameters		
Power supply		100 – 240 V AC 50/60 Hz and battery
Power consumption max.		5 W
Operation time on batteries		max 8h
Environmental conditions		
Operating temperature		-10 – +40 °C
Relative humidity		10% – 85% RH no condensation



Additional fee for verification



Accessories (Additional Fee)

Power Adapters
 RS 232 cables (scale - printer)
 Stands, wall mounting kits and mounting brackets
 Cigarette lighter receptacle power supply cables
 Displays
 RS 232, RS 485 cables




RS 232 – Ethernet Converter
 AP2-1 Current Loop Unit
 RS 232 – USB Converter
 RS 232 – RS 485 Converter
 Receipt Printer

Software (Additional Fee)

• RAD Key [WX-010-0005]
 • Scale Editor 2.1 [WX-010-0173]

• R-Lab [WX-010-0080]

Device dimensions W x D x H



Warunki transportu i przemieszczania wagi paletowej przy pomocy kółek jezdnych oraz uchwytów.

Transport of the pallet scale using casters and handles.