



More information on the website
mirror.radwag.com/en/info,w1,2X0

MAS.M.110.R2 Weighing Module

WX-016-0332



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	110 g
Preload range	11 g
Readability [d]	0.1 mg
Repeatability	0.1 mg
Linearity	±0.2 mg
Warm-up time after connection to power	1 h
Stabilization time	2 s
Adjustment	internal
Construction	
Protection class	IP 43
Housing	aluminum
Weighing pan material	aluminum
Communication interface	
Communication interface	RS232, max 115.2 kbps, Radwag ASCII protokół

Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 0.6A; 12V DC 1.2A Moduł: 12V DC
Environmental conditions	
Operating temperature	+10 – +40 °C
Relative humidity	40% – 80%
Physical parameters	
Weighing pan dimensions	ø40 mm
Device dimensions	220x70x100 mm
Net weight	1.6 kg



Accessories (Additional Fee)

RS 232, RS 485 cables

Software (Additional Fee)

• R-Panel [WX-010-0187]

Device dimensions

