



More information on the website
mirror.radwag.com/us/info,w1,2XB

SAL/T – Anti-vibration table in mild steel technology



The drawings, photos and graphics used are for illustrative purposes only.



Datasheet

| Construction | |
|-----------------------|-----------------|
| Construction | mild steel St3S |
| Load-bearing capacity | 40 kg |
| Physical parameters | |
| Packaging dimensions | 820×681×816 mm |
| Net weight | 55 kg |
| Gross weight | 68,5 kg |
| Length | 770 mm |
| Width | 650 mm |
| Height | 815±10 mm |

Compatible with

Automatic feeders

Device dimensions



SAL/T
