



More information on the website
mirror.radwag.com/us/info,w1,303

WAY 2.5Y.KO Mass Comparator



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

E1	1 – 2 kg
E2	500 g – 2 kg
F1	100 g – 2 kg
F2	10 g – 2 kg
M1	1 g – 2 kg
M2	1 g – 2 kg
Maximum capacity [Max]	2,3 kg
Readability [d]	0,1 mg
Standard repeatability [5% Max]	0,08 mg
Standard repeatability [Max]	0,1 mg
Permissible repeatability	0,2 mg
Eccentricity (tested load)	0 mg*
Electric compensation range	-50 g – +300 g
Stabilization time	20 s
Adjustment	internal

Physical parameters	
Display	10" graphic colour touchscreen
Weighing pan dimensions	ø70 mm
Weighing device dimensions	385×215×525 mm
Controlling device dimensions	249×170×72 mm
Anti-draft chamber dimensions	660×470×700 mm
Packaging dimensions	945×820×1260 mm
Chamber packaging size	820×850×630 mm
Net weight	39,5 kg
Gross weight	59,5 kg
Supplementary weights internal	automatic
Supplementary weights external	2×100 g
Communication interface	
2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot	
Operating temperature	
+15 – +30 °C	
Operating temperature change rate	
±0,5 °C / 12 h (±0,3 °C / 4 h)	
Relative humidity	
40% – 60%	
Relative humidity change rate	
±3% / 4 h	

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

Suspended Self-Centring Weighing Pan for WAY 5Y.KO Manual Mass Comparator	Label Printers
RFID Tags	THBR 2.0 System - Ambient Conditions Monitoring Receipt Printer
Antivibration tables	Fingerprint Reader
Additional modules	RS 232, RS 485 cables
Protective cover for balances	RS 232 cables (scale - printer)
Barcode scanners	
RS 232, RS 485 cables	

Software

- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]
- RMCS Lite [WX-010-0164]

Device dimensions




WAY 5.5Y.KO



WAY 100.5Y.KO



WAY 1200.5Y.KO



WAY 5100.5Y.KO

