



More information on the website
mirror.radwag.com/us/info,w1,36D

UYA 6.5Y Ultra-Microbalance

WL-109-0002



The drawings, photos and graphics used are for illustrative purposes only.

Functions

- Autotest
- Dosing
- Percent Weighing
- Parts counting
- Peak hold
- Formulation
- Newton unit measurement
- Statistics
- Checkweighing
- IR sensors
- GLP Procedures
- Animal weighing
- Pipettes Calibration
- Air density correction
- Density determination
- Differential weighing
- Ambient conditions monitoring
- Statistical Quality Control
- Packaged Goods Control
- ALIBI Memory
- Wi-Fi

Datasheet

Maximum capacity [Max]	6,1 g
Minimum load	0,01 mg
Readability [d]	0,1 µg

Verification unit [e]	1 mg
Tare range	-6,1 g
Standard repeatability [5% Max]	0,2 µg
Standard minimum weight (USP)	0,4 mg
Standard minimum weight (U=1%, k=2)	0,04 mg
Permissible repeatability [5% Max]	0,4 µg
Linearity	±1,5 µg
Eccentric load deviation	1,5 µg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	4 – 12 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Delivery components	Ultra-microbalance, terminal, weighing pan, weighing pan shield, glass lid, power supply, anti-draft shield, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø 90×90 mm
Weighing pan dimensions	ø16 mm
Anti-draft chamber dimensions	560×350×252 mm
Packaging dimensions W x D x H	750×492×595 mm
Net weight	10,6 kg
Gross weight	16,5 kg
Construction	
Protection class	IP 43
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A Max; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max; 9 – 17W*
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3 °C / 1 h (±1 °C / 8 h)
Relative humidity	40% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Accessories (Additional Fee)

MediaBox
RFID Tags
Antivibration tables

!Balance Storage Case
RS 232, RS 485 cables
Label Printers

Power Adapters
Additional modules
Professional Weighing Tables
Antistatic ionizer
Protective cover for balances
Barcode scanners

Chamber for filter weighing
THBR 2.0 System - Ambient Conditions Monitoring
Weighing dishes
Receipt Printer
Fingerprint Reader

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

Device dimensions W x D x H

