



More information on the website
mirror.radwag.com/us/info,w1,3B2

MPS.M.5100/10000.R22 Weighing Module

WX-016-1003



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	5100 / 10000 g
Preload range	1000 g
Readability [d]	0,01 / 0,05 g
Repeatability	0,01 / 0,05 g
Linearity	±20 / 50 mg
Warm-up time after connection to power	1 h
Stabilization time	2 s
Adjustment	internal
Construction	
Protection class	IP 43
Housing	aluminum
Weighing pan material	aluminum
Communication interface	
Communication interface	RS232

Electrical parameters

Power supply Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Module: 12V DC

Environmental conditions

Operating temperature +10 – +40 °C

Relative humidity 40% – 80%

Physical parameters

Weighing pan dimensions \varnothing 100 mm

Device dimensions W x D x H 266x70x105 mm

Net weight 1,8 kg



Accessories (Additional Fee)

RS 232, RS 485 cables
Antivibration tables

R Terminal (WDM-8)

Software (Additional Fee)

• R Panel [WX-010-0187]

Device dimensions W x D x H

