



More information on the website
mirror.radwag.com/us/info,w1,452

XA 21/52.5Y.M.A Microbalance

WL-109-1004



The drawings, photos and graphics used are for illustrative purposes only.

Functions

- | | | | |
|---|---|---|--|
|  Autotest |  Dosing |  Percent Weighing |  Parts counting |
|  Peak hold |  Formulation |  Newton unit measurement |  Statistics |
|  Checkweighing |  IR sensors |  GLP Procedures |  Animal weighing |
|  Pipettes Calibration |  Air density correction |  Automatic sliding door |  Density determination |
|  Differential weighing |  Ambient conditions monitoring |  Statistical Quality Control |  Packaged Goods Control |
|  ALIBI Memory |  Wi-Fi | | |

Datasheet

Maximum capacity [Max]	21 / 52 g
Minimum load	0,1 mg
Readability [d]	1 / 5 µg

Verification unit [e]	1 mg
Tare range	-52 g
Standard repeatability [5% Max]	1,5 µg
Standard minimum weight (USP)	3 mg
Standard minimum weight (U=1%, k=2)	0,3 mg
Permissible repeatability [5% Max]	2,4 µg
Linearity	±20 µg
Eccentric load deviation	20 µg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times R_t$
Stabilization time	~ 3,5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, weighing pan, weighing pan shield, power supply, brush, fabric dust cover.
Weighing chamber dimensions	199×170×217 mm
Weighing pan dimensions	ø30 mm
Packaging dimensions W x D x H	750×492×595 mm
Net weight	14,5 kg
Gross weight	18,9 kg
Construction	
Protection class	IP 43
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A Max; 15V DC 2,4A Balance: 12 – 15V DC 1,6A max; 10 – 19W*
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3 °C / 1 h (±1 °C / 8 h)
Relative humidity	40% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Accessories (Additional Fee)

MediaBox
 RFID Tags
 Antivibration tables
 Power Adapters
 Protective cover for balances
 RS 232, RS 485 cables
 Additional modules
 Anti-Draft Chamber for Microbalances
 Professional Weighing Tables
 Barcode scanners
 Automatic feeders

MICRO-KIT - Set of Holders for Microscale Glassware
 Label Printers
 THBR 2.0 System - Ambient Conditions Monitoring
 Adapters for pipettes calibration
 Anti-Draft Chamber for XA 4Y and XA 5Y Balances
 Weighing dishes
 Antistatic ionizer
 Receipt Printer
 Fingerprint Reader
 RS 232 – USB Converter
 Under-pan weighing

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

Device dimensions W x D x H

