



More information on the website
mirror.radwag.com/en/info,w1,4NG

HX5.EX-1.1,5.H1 One Load Cell Platform Scale

WW-006-0017



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	1.5 kg
Minimum load	10 g
Readability [d]	0.5 g
Verification unit [e]	0.5 g
Tare range	-1.5 kg
OIML Class	III

Physical parameters	
Display	5" graphic colour
Cable length	1.5 m
Weighing pan dimensions	150×200 mm
Packaging dimensions W x D x H	310×640×460 mm
Net weight	11.5 kg
Gross weight	12.5 kg
Construction	
Protection class	IP 66 / 67 construction, IP 66 / 68 terminal
ATEX Certification	II 2G Ex ib IIB T4 Gb
IECEx Certification	Ex ib IIB T4 Gb
Construction	Stainless steel AISI304
Weighing pan material	Stainless steel AISI304
Communication interface	
Communication interface	2×RS232, RS485
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Power consumption max.	15 W
Environmental conditions	
Operating temperature	-10 – +40 °C
Relative humidity	10% – 85% RH no condensation
Indicator	PUE HX5.EX-1



Additional fee for verification



Accessories (Additional Fee)

Communication Modules
 Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX
 Weighing Terminal

Receipt Printer

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]