




More information on the website
mirror.radwag.com/tr/info,w1,5AH

DWT/RC 600 HYK dinamik ray kantarı

WK-106-____



The drawings, photos and graphics used are for illustrative purposes only.

Teknik Veriler

Metrolojik parametreler

Maksimum yük [Max]	600 kg
Dara aralığı	-600 kg

Fiziksel parametreler

Display	10,1" grafik renkli dokunmatik
---------	--------------------------------



Aksesuarlar (Additional Fee)

Display
Transponder kart okuyucular
RS 232 Kablolari (Teraziler - ZEBRA Yazıcı)

RS 232, RS 485 Kablolari
Fiş yazıcı
USB Kablolar (terazi-Epson yazıcı)