



More information on the website  
[mirror.radwag.com/tr/info,w1,5ED](http://mirror.radwag.com/tr/info,w1,5ED)

# HX5.EX-1.60.HR3/5 Tek Yük Hücreli Platform Terazi

WW-007-0016



The drawings, photos and graphics used are for illustrative purposes only.

## Fonksiyonlar



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

## Teknik Veriler

| Metrolojik parametreler  |        |
|--------------------------|--------|
| Maksimum yük [Max]       | 60 kg  |
| Minimum yük [Min]        | 400 g  |
| Okuma içingruluđu [d]    | 20 g   |
| Yasallaştırma birimi [e] | 20 g   |
| Dara aralığı             | -60 kg |
| OIML sınıfı              | III    |

| Fiziksel parametreler       |   |
|-----------------------------|---|
| Display                     | 5" grafik renkli                                    |
| Kablo uzunluđu              | 2,5 m   |
| Tartım kefesi boyutları     | 400x600 mm  |
| Ambalaj boyutları G x D x Y | 490x680x450 mm                                      |
| Konstrüksiyon               |   |
| IP Sınıfı                   | IP 66 / 67 / 69 konstrüksiyon, IP 66 / 68 terminal  |
| Sertifikasyon ATEX          | II 2G Ex ib IIC T4 Gb<br>II 2D Ex ib IIIC T135°C Db |
| Sertifikasyon IECEx         | Ex ib IIC T4 Gb<br>Ex ib IIIC T135°C Db             |
| Konstrüksiyon               | Paslanmaz çelik AISI316                             |
| Tartım kefesi               | Paslanmaz çelik AISI316                             |
| Haberleşme arayüzler        |   |
| Haberleşme arayüzü          | 2xRS232, RS485                                      |
| Elektrik parametreleri      |   |
| Güç kaynađı                 | 100 – 240 V AC 50/60 Hz                             |
| Maksimum güç tüketimi       | 15 W  |
| Çevresel koşullar           |   |
| Çalıştırma sıcaklığı        | -10 – +40 °C  |
| Atmosferik nem              | 10% – 85% RH yoğunlaşma yok                         |
| İndikatör                   | PUE HX5.EX-1  |



Additional fee for verification



## Aksesuarlar (Additional Fee)

Haberleşme modülü  
Terazi için tasarlanmış kendinden korumalı güç kaynađı

Fiş yazıcı

## Yazılım (Additional Fee)

- E2R Tartım [WX-010-0099]
- Etiket Editörü R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]
- RAD Key [WX-010-0005]
- Alibi Okuyucu PC Yazılımı [WX-010-0114]
- Terazi Editörü - EWAG 2.1 [WX-010-0173]

# Cihaz boyutları G x D x Y

| Scale type     | A1  | A2  | B     |
|----------------|-----|-----|-------|
| HX5.EX-1.HR2   | 250 | 300 | 103±3 |
| HX5.EX-1.HR3   | 410 | 410 | 98±2  |
| HX5.EX-1.HR4   | 500 | 500 | 155±5 |
| HX5.EX-1.HR3/5 | 400 | 600 | 155±5 |
| HX5.EX-1.HR5   | 600 | 600 | 155±5 |

Dimensions in mm



PUE HX5.EX-1



Platform H