



More information on the website
mirror.radwag.com/us/info,w1,5R5

DWM/HPW Checkweigher

WK-105-001_



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| | |
|----------------------------|--------------------------------|
| Maximum capacity [Max] | 750 – 7500 g |
| Readability [d] | 0,1 – 5 g |
| Tare range | -750 – -7500 g |
| Physical parameters | |
| Display | 12" graphic colour touchscreen |
| Construction | |
| Protection class | IP 55, IP 65, IP 69k |
| Operating temperature | 0 – +40 °C |
| Operating system | Microsoft Windows 11 IoT |
| Features of use | |
| Capacity | max 400 pcs/min |
| Speed | 0,1 – 1,6 m/s |



Accessories (Additional Fee)

Displays

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Barcode scanners

Label Printers

Keypad, external switches

USB adapter

Receipt Printer

USB cable (scale - printer)

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]