



More information on the website
mirror.radwag.com/us/info,w1,5R5

DWM/HPW Checkweigher

WK-105-001_



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]	750 – 7500 g
Readability [d]	0,1 – 5 g
Tare range	-750 – -7500 g
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 55, IP 65, IP 69k
Operating temperature	0 – +40 °C
Operating system	Microsoft Windows 11 IoT
Features of use	
Capacity	max 400 pcs/min
Speed	0,1 – 1,6 m/s



Accessories (Additional Fee)

Displays

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Barcode scanners

Label Printers

Keypad, external switches

USB adapter

Receipt Printer

USB cable (scale - printer)

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]