



More information on the website
mirror.radwag.com/en/info,w1,5WG

C315.60/150.C2.K Load Cell Platform Scale

WP-123-1017



The drawings, photos and graphics used are for illustrative purposes only.

Functions

 Plus/Minus Control

 Percent Weighing

 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 GLP Procedures

 Animal weighing

 ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	60 / 150 kg
Minimum load	400 g
Readability [d]	20 / 50 g
Verification unit [e]	20 / 50 g
Tare range	-150 kg
OIML Class	III

Physical parameters		
Display		4.3" LCD (backlit)
Cable length		2.5 m
Weighing pan dimensions		400×500 mm
Packaging dimensions W x D x H		720×620×210 mm
Net weight		12.5 kg
Gross weight		15 kg
Construction		
Protection class		IP 65 construction, IP 43 terminal
Construction		mild steel St3S
Weighing pan material		Stainless steel AISI304
Communication interface		
Communication interface		RS232
Optional interfaces		RS232
Electrical parameters		
Power supply		100 – 240 V AC 50/60 Hz and battery
Power consumption max.		5 W
Operation time on batteries		max 8h
Environmental conditions		
Operating temperature		-10 – +40 °C
Storage temperature		-10 – +50 °C
Relative humidity		10% – 85% RH no condensation
Indicator		C315



Additional fee for verification



Accessories (Additional Fee)



Antivibration Tables
 Power Adapters
 RS 232 cables (scale - printer)
 Stands, wall mounting kits and mounting brackets
 Cigarette lighter receptacle power supply cables
 Displays

RS 232, RS 485 cables
 RS 232 – Ethernet Converter
 AP2-1 Current Loop Unit
 RS 232 – USB Converter
 RS 232 – RS 485 Converter
 Receipt Printer


Software (Additional Fee)

• RAD Key [WX-010-0005]
 • Scale Editor 2.1 [WX-010-0173]



• R-Lab [WX-010-0080]




C315.F1.M



C315.F1.R




C315.C2.M




C315.C2.K



Device dimensions W x D x H





C315.C2.R



C315.C2.K



C315.C3.M



C315.C3.K