



More information on the website
mirror.radwag.com/en/info,w1,6M9

Dust-Free Cabinet for Printers

WX-007-0047



The drawings, photos and graphics used are for illustrative purposes only.

Overview

Dust-free cabinet is applicable as means of protecting the printers against operation in heavily dusted areas. The airtight shield made of stainless steel protects a printer against defects, and allows for operation in not adapted places.

Compatible with (Additional Fee)

Label Printers

Device dimensions W x D x H

DR-1 - Citizen CLP-521, CLP-621, CLP-631, CL-S521, CL-S621, CL-S631
 DR-2 - Citizen CLP-7201
 DR-3 - Citizen CL-S700
 DR-4 - Citizen CL-S700R
 DR-5 - Zebra GK 420d; GK 420t; GX 420d; GX420t; GX 430t
 DR-6 - Zebra ZT 220; ZT 230
 DR-7 - Zebra ZM 440.

Symbol	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	G [mm]	masa [kg]
DR-1	300	400	430	245	275	min 350	~95	15
DR-2	360	400	600	305	275	min 500	~95	22
DR-3	360	400	670	305	275	min 550	~95	24
DR-4	360	525	670	305	400	min 550	~95	27
DR-5	270	330	380	215	205	min 300	~95	13
DR-6	330	430	600	275	305	min 500	~95	22
DR-7	360	490	670	305	365	min 550	~95	26

