



More information on the website  
[mirror.radwag.com/en/info,w1,6M9](https://mirror.radwag.com/en/info,w1,6M9)

## Dust-Free Cabinet for Printers

WX-007-0047



The drawings, photos and graphics used are for illustrative purposes only.

### Overview

Dust-free cabinet is applicable as means of protecting the printers against operation in heavily dusted areas. The airtight shield made of stainless steel protects a printer against defects, and allows for operation in not adapted places.

### Compatible with (Additional Fee)

Label Printers

### Device dimensions

DR-1 - Citizen CLP-521, CLP-621, CLP-631, CL-S521, CL-S621, CL-S631  
 DR-2 - Citizen CLP-7201  
 DR-3 - Citizen CL-S700  
 DR-4 - Citizen CL-S700R  
 DR-5 - Zebra GK 420d; GK 420t; GX 420d; GX420t; GX 430t  
 DR-6 - Zebra ZT 220; ZT 230  
 DR-7 - Zebra ZM 440.

| Symbol | A [mm] | B [mm] | C [mm] | D [mm] | E [mm] | F [mm]  | G [mm] | masa [kg] |
|--------|--------|--------|--------|--------|--------|---------|--------|-----------|
| DR-1   | 300    | 400    | 430    | 245    | 275    | min 350 | ~95    | 15        |
| DR-2   | 360    | 400    | 600    | 305    | 275    | min 500 | ~95    | 22        |
| DR-3   | 360    | 400    | 670    | 305    | 275    | min 550 | ~95    | 24        |
| DR-4   | 360    | 525    | 670    | 305    | 400    | min 550 | ~95    | 27        |
| DR-5   | 270    | 330    | 380    | 215    | 205    | min 300 | ~95    | 13        |
| DR-6   | 330    | 430    | 600    | 275    | 305    | min 500 | ~95    | 22        |
| DR-7   | 360    | 490    | 670    | 305    | 365    | min 550 | ~95    | 26        |

