



More information on the website
mirror.radwag.com/en/info,w1,6M9

Dust-Free Cabinet for Printers

WX-007-0047



The drawings, photos and graphics used are for illustrative purposes only.

Overview

Dust-free cabinet is applicable as means of protecting the printers against operation in heavily dusted areas. The airtight shield made of stainless steel protects a printer against defects, and allows for operation in not adapted places.

Compatible with (Additional Fee)

Label Printers

Device dimensions W x D x H

DR-1 - Citizen CLP-521, CLP-621, CLP-631, CL-S521, CL-S621, CL-S631
 DR-2 - Citizen CLP-7201
 DR-3 - Citizen CL-S700
 DR-4 - Citizen CL-S700R
 DR-5 - Zebra GK 420d; GK 420t; GX 420d; GX420t; GX 430t
 DR-6 - Zebra ZT 220; ZT 230
 DR-7 - Zebra ZM 440.

| Symbol | A [mm] | B [mm] | C [mm] | D [mm] | E [mm] | F [mm] | G [mm] | masa [kg] |
|--------|--------|--------|--------|--------|--------|---------|--------|-----------|
| DR-1 | 300 | 400 | 430 | 245 | 275 | min 350 | ~95 | 15 |
| DR-2 | 360 | 400 | 600 | 305 | 275 | min 500 | ~95 | 22 |
| DR-3 | 360 | 400 | 670 | 305 | 275 | min 550 | ~95 | 24 |
| DR-4 | 360 | 525 | 670 | 305 | 400 | min 550 | ~95 | 27 |
| DR-5 | 270 | 330 | 380 | 215 | 205 | min 300 | ~95 | 13 |
| DR-6 | 330 | 430 | 600 | 275 | 305 | min 500 | ~95 | 22 |
| DR-7 | 360 | 490 | 670 | 305 | 365 | min 550 | ~95 | 26 |

