




More information on the website  
[mirror.radwag.com/tr/info,w1,6M9](http://mirror.radwag.com/tr/info,w1,6M9)

## Yazıcılar için Toz sızdırmaz Kabin

WX-007-0047



The drawings, photos and graphics used are for illustrative purposes only.

### Genel Açıklama

Dust-free cabinet is applicable as means of protecting the printers against operation in heavily dusted areas. The airtight shield made of stainless steel protects a printer against defects, and allows for operation in not adapted places.

### İle uyumlu (Additional Fee)

Etiket Yazıcısı

# Cihaz boyutları G x D x Y

DR-1 - Citizen CLP-521, CLP-621, CLP-631, CL-S521, CL-S621, CL-S631  
 DR-2 - Citizen CLP-7201  
 DR-3 - Citizen CL-S700  
 DR-4 - Citizen CL-S700R  
 DR-5 - Zebra GK 420d; GK 420t; GX 420d; GX420t; GX 430t  
 DR-6 - Zebra ZT 220; ZT 230  
 DR-7 - Zebra ZM 440.

Symbol	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	G [mm]	masa [kg]
DR-1	300	400	430	245	275	min 350	~95	15
DR-2	360	400	600	305	275	min 500	~95	22
DR-3	360	400	670	305	275	min 550	~95	24
DR-4	360	525	670	305	400	min 550	~95	27
DR-5	270	330	380	215	205	min 300	~95	13
DR-6	330	430	600	275	305	min 500	~95	22
DR-7	360	490	670	305	365	min 550	~95	26

