



PL.1100.HRP

WX-009-0152

More information on the website  
[mirror.radwag.com/ja/info,w1,783](http://mirror.radwag.com/ja/info,w1,783)



The drawings, photos and graphics used are for illustrative purposes only.

Table

Name	
Capacity [Max]	1100 kg
Capacity	100 kg
Resolution [d]	10 g
Capacity	-1100 kg
Capacity	15 g
Capacity	±30 g
Capacity	Capacity (Capacity)
Capacity	
Capacity	IP 67
Capacity	Capacity St3S
Capacity	Capacity AISI304
Capacity	
Capacity	RS232, RS485, Ethernet

Electrical

Voltage 100 – 240 V AC 50/60 Hz

Environment

Temperature +10 – +40 °C

Humidity 15% – 80%

Mechanical

Width 1000x800 mm

Height 1000x1200x436 mm

Weight 126 kg

Max. weight 160 kg



Options (Additional Fee)

PGC-CY10
RS 232 (RJ45 - RJ45)
PUE 7.1
RS 232/RS 485
IN/OUT

PUE HY10
PUE HX5.EX
CY10
RS 232 – USB

Accessories (Additional Fee)

- MWMH Manager [WX-010-0103]
• RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]





PL.16 - 32.HRP



PL.62-2000.HRP

Scale type	A1	A2	H
PL.(16-32).HRP	360	280	180±5
PL.(62-150).HRP	500	400	180±5
PL.150.2.HRP	500	500	180±5
PL.(150.1-300).HRP	800	600	180±5
PL.(300.1-1100).HRP	1000	800	180±5
PL.(2000).HRP	1250	1000	180±5

Dimensions in mm