



More information on the website  
[mirror.radwag.com/tr/info,w1,791](http://mirror.radwag.com/tr/info,w1,791)

## C315.4.600.C7 Yer kantarı

WP-230-0007



The drawings, photos and graphics used are for illustrative purposes only.

### Fonksiyonlar

 Plus/Minus Control

 Percent Weighing


 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 GLP Procedures

 Animal weighing

 ALIBI Memory

### Teknik Veriler

#### Metrolojik parametreler

|   |         |
|---|---------|
| Maksimum yük [Max]  | 600 kg  |
| Minimum yük [Min]   | 4 kg    |
| Okuma için doğruluğu [d]                                    | 0,2 kg  |
| Yasallaştırma birimi [e]                                    | 0,2 kg  |
| Dara aralığı  | -600 kg |
| Ticari amaçla kullanılmayan terazi için maksimum hassasiyet | 50 g    |
| OIML sınıfı   | III     |

| Fiziksel parametreler          |  |
|--------------------------------|--|
| Display                        | 4,3" LCD (aydınlatma ile)                                |
| Kablo uzunluğu                 | 3 m  |
| Tartım kefi boyutları          | 1000x1000 mm   |
| Tartım platformunun yüksekliđi | 120 ± 10 mm  |
| Ambalaj boyutları G x D x Y    | 1100x1000x500 mm   |
| Göstergeli terazi kütlesi      | 80 kg  |
| Konstrüksiyon                  |  |
| IP Sınıfı                      | IP 65 konstrüksiyon, IP 67 gerinim ölçer, IP 43 terminal |
| Haberleşme arayüzler           |  |
| Haberleşme arayüzü             | RS232  |
| Opsiyonel arayüzler            | RS232  |
| Elektrik parametreleri         |  |
| Güç kaynađı                    | 100 – 240 V AC 50/60 Hz + batarya                        |
| Maksimum güç tüketimi          | 5 W  |
| Batarya ile çalışma süresi     | max 8h   |
| Çevresel koşullar              |  |
| Çalıştırma sıcaklığı           | -10 – +40 °C   |
| Atmosferik nem                 | 10% – 85% RH yoğunlaşma yok                              |



Additional fee for verification



## Aksesuarlar (Additional Fee)

Güç adaptörü  
RS 232 Kablolar (Teraziler - Yazıcı)  
Tartım terminalleri için tutucular  
Çakmak prizine uygun besleme kabloları  
Display  
Rampa  
RS 232, RS 485 Kabloları

RS 232 – Ethernet Dönüştürücü  
Teraziye yere batırmak için çerçeve  
AP2-1 Güç döngüsü çıkışı  
RS 232 – USB Dönüştürücü  
Kablolar RS 232 (Teraziler - Yazıcı)  
RS 232 – RS 485 Dönüştürücü  
Fiş yazıcı

## Yazılım (Additional Fee)

• RAD Key [WX-010-0005]  
• Terazi Editörü - EWAG 2.1 [WX-010-0173]

• R-Lab [WX-010-0080]

## Cihaz boyutları G x D x Y



|         | A    | B    | H       |
|---------|------|------|---------|
| C6      | 800  | 800  | 120 ±10 |
| C7      | 1000 | 1000 | 120 ±10 |
| C8      | 1200 | 1200 | 120 ±10 |
| C8/9    | 1200 | 1500 | 120 ±10 |
| C9      | 1500 | 1500 | 120 ±10 |
| 6000.C9 | 1500 | 1500 | 160 ±10 |