



High Resolution Platforms PL.32.HRP.EX

WX-009-0272

More information on the website
mirror.radwag.com/us/info,w1,7E5



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| | |
|--------------------------------|----------------------|
| Maximum capacity [Max] | 32 kg |
| Preload range | 4 kg |
| Readability [d] | 0,1 g |
| Tare range | -32 kg |
| Repeatability | 0,1 g |
| Linearity | ±0,3 g |
| Adjustment | internal (automatic) |
| Physical parameters | |
| Cable length | 10 m |
| Weighing pan dimensions | 360×280 mm |
| Packaging dimensions W x D x H | 560×473×370 mm |
| Net weight | 14,6 kg |
| Gross weight | 18,6 kg |
| Construction | |
| Protection class | IP 67 |

| Construction | |
|-------------------------|-------------------------|
| ATEX Certification | II 3G Ex ic IIB T4 Gc |
| IECEX Certification | Ex ic IIB T4 Gc |
| Construction | aluminum |
| Weighing pan material | Stainless steel AISI304 |
| | |
| Communication interface | RS485 |
| | |
| Power supply | 100 – 240 V AC 50/60 Hz |
| | |
| Operating temperature | +10 – +40 °C |
| Relative humidity | 15% – 80% |



Accessories (Additional Fee)

PUE HX5.EX Weighing Terminal
Antivibration tables



Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX
Weighing Terminal
Receipt Printer

Software (Additional Fee)



- MWMH Manager [WX-010-0103]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]

Device dimensions W x D x H



PL.16 - 32.HRP



PL.62-2000.HRP

| Scale type | A1 | A2 | H |
|---------------------|------|------|-------|
| PL.(16-32).HRP | 360 | 280 | 180±5 |
| PL.(62-150).HRP | 500 | 400 | 180±5 |
| PL.150.2.HRP | 500 | 500 | 180±5 |
| PL.(150.1-300).HRP | 800 | 600 | 180±5 |
| PL.(300.1-1100).HRP | 1000 | 800 | 180±5 |
| PL.(2000).HRP | 1250 | 1000 | 180±5 |

Dimensions in mm