



More information on the website  
[mirror.radwag.com/br/info,w1,850](http://mirror.radwag.com/br/info,w1,850)

# Plataforma de pesagem C315.4.150.C6

WP-230-0001



The drawings, photos and graphics used are for illustrative purposes only.

## Funções



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit  
measurement



GLP Procedures



Animal weighing



ALIBI Memory

## Ficha Técnica

| Parâmetros metrológicos                         |         |
|-------------------------------------------------|---------|
| Capacidade máxima [máx]                         | 150 kg  |
| Carga mínima                                    | 1 kg    |
| Resolução [d]                                   | 0,05 kg |
| Unidade de verificação [e]                      | 0,05 kg |
| Faixa de tara                                   | -150 kg |
| Resolução máxima para plataforma não verificada | 20 g    |
| Classe OIML                                     | III     |

| Parâmetros físicos               |                                                |
|----------------------------------|------------------------------------------------|
| Display                          | 4,3" LCD (retroiluminado)                      |
| Comprimento até cabo             | 3 m                                            |
| Dimensões até prato de pesagem   | 800×800 mm                                     |
| Altura da plataforma de pesagem  | 116 ± 6 mm                                     |
| Dimensões da embalagem L x P x A | 900×900×500 mm                                 |
| Plataforma com indicador         | 55 kg                                          |
| Construção                       |                                                |
| Classe de proteção               | IP 65 construção, IP 67 célula, IP 43 terminal |
| Interface de comunicação         |                                                |
| Interface de comunicação         | RS232                                          |
| Interfaces opcionais             | RS232                                          |
| Parâmetros elétricos             |                                                |
| Fonte de alimentação             | 100 – 240 V AC 50/60 Hz e bateria              |
| Consumo de energia máx.          | 5 W                                            |
| Tempo de operação com baterias   | max 8h                                         |
| Condições ambientais             |                                                |
| Temperatura de operação          | -10 – +40 °C                                   |
| Umidade relativa                 | 10% – 85% RH sem condensação                   |



Additional fee for verification



## Acessórios (Additional Fee)

Adaptadores de energia  
Cabos de alimentação para acendedor de cigarro automotivo  
Displays  
RS 232, RS 485 cabos  
Conversor RS 232 – Ethernet


RS 232 – Conversor USB  
Cabos RS 232 (plataforma - impressora)  
Conversor RS 232 – RS 485  
Impressora de recibos

## Software (Additional Fee)

• RAD Key [WX-010-0005]

• R-Lab [WX-010-0080]

Dimensões do dispositivo L x P x A



|         | A    | B    | H       |
|---------|------|------|---------|
| C6      | 800  | 800  | 120 ±10 |
| C7      | 1000 | 1000 | 120 ±10 |
| C8      | 1200 | 1200 | 120 ±10 |
| C8/9    | 1200 | 1500 | 120 ±10 |
| C9      | 1500 | 1500 | 120 ±10 |
| 6000.C9 | 1500 | 1500 | 160 ±10 |