



More information on the website  
[mirror.radwag.com/en/info,w1,8LG](https://mirror.radwag.com/en/info,w1,8LG)

# H315.4.150.H7/Z Stainless Steel Platform Scale, pit version

WP-233-0004



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit measurement



Animal weighing

## Datasheet

| Metrological parameters                |         |
|----------------------------------------|---------|
| Maximum capacity [Max]                 | 150 kg  |
| Minimum load                           | 1 kg    |
| Readability [d]                        | 50 g    |
| Verification unit [e]                  | 50 g    |
| Tare range                             | -150 kg |
| Max readability for non-verified scale | 20 g    |
| OIML Class                             | III     |

| Physical parameters                 |                                                                 |
|-------------------------------------|-----------------------------------------------------------------|
| Display                             | 4.3" LCD (backlit)                                              |
| Cable length                        | 3 m                                                             |
| Weighing pan dimensions             | 1000×1000 mm                                                    |
| Weighing platform height            | 88 mm                                                           |
| Packaging dimensions W x D x H      | 1200×1200×530 mm                                                |
| Scale mass with indicator and frame | 105 kg                                                          |
| Construction                        |                                                                 |
| Protection class                    | IP 66 / 69 construction, IP 66 / 67 / 69 terminal               |
| Communication interface             |                                                                 |
| Communication interface             | RS232, USB                                                      |
| Optional interfaces                 | RS232 or RS485 or 4IN/4OUT or Ethernet or analog output 4-20 mA |
| Electrical parameters               |                                                                 |
| Power supply                        | 100 – 240 V AC 50/60 Hz                                         |
| Optional power supply               | internal rechargeable battery                                   |
| Operation time on batteries         | max 7h                                                          |
| Environmental conditions            |                                                                 |
| Operating temperature               | -10 – +40 °C                                                    |
| Relative humidity                   | 10% – 85% RH no condensation                                    |



Additional fee for verification



## Accessories (Additional Fee)

AP2-4 Current Loop Unit  
 RS 232 cables (scale - printer)  
 Displays  
 Ethernet cables (scale - Ethernet)  
 RS 232, RS 485 cables  
 Power Adapters


RS 232 – Ethernet Converter  
 USB adapter  
 Receipt Printer  
 USB cable (scale - printer)  
 Stands, wall mounting kits and mounting brackets  
 RS 232 – USB Converter

## Software (Additional Fee)




• RAD Key [WX-010-0005]  
 • Scale Editor 2.1 [WX-010-0173]

• R-Lab [WX-010-0080]

Device dimensions W x D x H



Single-leaf platform:  
H315.4.H6/Z  
H315.4.H7/Z  
H315.4.H8/Z



Double-leaf platform:  
H315.4.H8/9/Z  
H315.4.H9/Z  
H315.4.H10/Z

| Scale type             | A    | B    | H      |
|------------------------|------|------|--------|
| H315.4.150-600.H6/Z    | 800  | 800  | 88±2   |
| H315.4.150-1500.H7/Z   | 1000 | 1000 | 88±2   |
| H315.4.300-1500.H8/Z   | 1200 | 1200 | 88 ±2  |
| H315.4.3000.H8/Z       | 1200 | 1200 | 111 ±2 |
| H315.4.300-1500.H8/9/Z | 1200 | 1500 | 88 ±2  |
| H315.4.3000.H8/9/Z     | 1200 | 1500 | 111 ±2 |
| H315.4.300-1500.H9/Z   | 1500 | 1500 | 88 ±2  |
| H315.4.3000-6000.H9/Z  | 1500 | 1500 | 111 ±2 |
| H315.4.600-6000.H10/Z  | 1500 | 2000 | 111 ±2 |

dimensions in mm