



More information on the website
mirror.radwag.com/en/info,w1,8UH

PL 0,6/1,5/D2 Platform

WX-009-1014



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	0.6 / 1.5 kg
Readability [d]	0.5 g
Construction	
Protection class	IP 43
Housing	ABS plastic
Weighing pan material	Stainless steel AISI304
Physical parameters	
Weighing pan dimensions	195×195 mm
Packaging dimensions W x D x H	530×310×150 mm

Readability accuracy – expected value, dependent on the parameters of the measuring transmitter used.





Accessories (Additional Fee)


CY10 Scales for PGC
 PUE CY10 Weighing Terminal
 CY10 Multifunctional Scale
 PUE 5 Weighing Terminal
 CY10 Precision Balance

PUE HX7 Weighing Terminal
 PUE C32 Weighing Terminal
 PUE 7.1 Weighing Terminal
 PUE HY10 Weighing Terminal
 RS 232 – USB Converter


Device dimensions W x D x H




PL/D2



PLC/F1



PLC/C2
PLC/C3



PL/H
PL/HR

Platform type	A1	A2	H
PL/D2	238	216	82±3
PLC/F1	300	300	70±3
PLC/C2	402	502	103±3
PLC/C3	701	501	130±5
PL/H1 / PL/HR1	150	200	85±3
PL/H2 / PL/HR2	250	300	103±3
PL/H3 / PL/HR/3	410	410	98±3
PL/H3/5 / PL/HR/3/5	400	600	155±3
PL/H4 / PL/HR/4	500	500	155±3
PL/H5 / PL/HR/5	600	600	155±3
PL/H6	800	800	135±3

dimensions in mm